



Powering Business Worldwide

pe.eaton.com

Capacitive Proximity Sensor

E53KAL30T111ED

UPC:782114012963

Dimensions:

- **Height:** 1.18 IN
- **Length:** 3.94 IN
- **Width:** 1.18 IN

Warranties:

- 1 year

Specifications:

- **Connection:** M12
- **Contact Rating:** 300 mA Solid State Output
- **Contact Configuration:** NO PNP open collector
- **Diameter:** 1.18110237 MM
- **Enclosure Material:** POM, mounting nuts, nylon PA66
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12, 13, IP65
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 300 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C and reverse polarity
- **Series:** E53

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Sensing solutions-versatile, robust and innovative](#)
- [Eaton Specification Sheet - E53KAL30T111ED](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.