



Powering Business Worldwide

pe.eaton.com

55 Series Photoelectric Sensor

1355R-6513

UPC:782114106952

Dimensions:

- **Height:** 3.19 IN
- **Length:** 1.83 IN
- **Width:** 1.64 IN

Weight: .5875 LB

Notes: Ranges based on 3-inch retroreflector for reflex sensors; 90% reflectance card for diffuse reflective sensors

Warranties:

- 3 year

Specifications:

- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 3A AC/DC at 120 Vac / 30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** SPDT Form C Relay
- **Cord Length:** 72 FT
- **Enclosure Material:** Body: Noryl, Lens: Nylon
- **Environmental Rating:** NEMA 1,3,4,6,12,13
- **Input Voltage:** 20–264 Vac 50/60 Hz or 15–30 Vdc (NPN)
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 3A
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - 1355R-6513](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance:

- Contact Manufacturer

© 2016 Eaton. All rights reserved.