



Powering Business Worldwide

pe.eaton.com

## CurrentWatch EAC Top Terminal Current Sensor

EAC1420SC

UPC:786685120560

### Dimensions:

- **Height:** 2.75 IN
- **Length:** 3.5 IN
- **Width:** 1.2 IN

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** 1.0% FS
- **Amperage Rating:** 10, 20, or 50A
- **Connection:** Screw Terminals
- **Enclosure:** Solid-Core housing
- **Contact Configuration:** 4-20mA analog output
- **Enclosure Material:** UL94 V0 flammability rated plastic
- **Input Voltage:** 24 Vdc loop powered
- **Maximum Ac Current:** 50A
- **Operating Temperature:** -4° to 122°F (-20° to 50°C)

### Supporting documents:

- [CurrentWatch current sensors](#)
- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - EAC1420SC](#)

**Certifications:** No Data

**Product compliance:** No Data

