



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Thermal-Magnetic Circuit Breaker

BAB3020HT

UPC:782114266045

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.9 IN
- **Width:** 3.1 IN

Weight:.95 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Special Features:** Ring or Spade Lug Terminals
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on
- **Quantity:** 8

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB3020HT](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



