



Powering Business Worldwide

pe.eaton.com

Adjustable Frequency Drive

SPX075A1-4A1N1

UPC:782116011919

Dimensions:

- **Height:** 30.1 IN
- **Length:** 13.5 IN
- **Width:** 11.5 IN

Weight:127 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR8
- **Horsepower:** 75 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 480V

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX075A1-4A1N1](#)
- [Product Datasheet - SPX075A1-4A1N1](#)

Certifications:

- IEC 61800-2
- UL 508C
- EN 61800-3 Level H
- UL Listed

Product compliance: No Data



