



Powering Business Worldwide

pe.eaton.com

Industrial Control Transformer

C0100E4H

UPC:786680004957

Dimensions:

- **Height:** 2.874 IN
- **Length:** 3.386 IN
- **Width:** 34.094 IN

Weight:4 LB

Notes:Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTE
- **Primary Voltage:** 380/400/415V
- **Secondary Voltage:** 22/23/24V
- **Tap Size:** None
- **Temperature Rating:** 55°C
- **Type:** Industrial Control Transformer
- **Volt Ampere Rating:** 100 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - C0100E4H](#)

Certifications:

- CSA Certified
- UL Listed



- cUL Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.