



Powering Business Worldwide

pe.eaton.com

General-Purpose Transformer

V48M28F45CUEELS42

UPC:786680033360

Dimensions:

- **Height:** 32.02 IN
- **Length:** 16.5 IN
- **Width:** 23 IN

Weight:441 LB

Notes:NEMA TP-1 efficient, Low sound equal to 42 dB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Dry Type Distribution Transformer
- **Design:** DT-3
- **Coil Material:** Copper windings
- **Frame:** 912B
- **Frequency Rating:** 60 Hz
- **Modification 1:** Low sound 42 dB
- **Phase:** Three-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 45 KVA
- **Weathershield:** WS38

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - V48M28F45CUEELS42](#)

Certifications:



- UL Listed

Product compliance:

- NEMA TP-1 Compliant

© 2016 Eaton. All rights reserved.