



Powering Business Worldwide

pe.eaton.com

Harsh Environment Non-Metallic Safety Switch

DH322FCK

UPC:782114295984

Dimensions:

- **Height:** 19.25 IN
- **Length:** 15.46 IN
- **Width:** 10.25 IN

Notes: Suitable for service entrance use with a neutral or ground lug kit installed

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Non-metallic
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Harsh Environment - EnviroLine
- **Voltage Rating:** 240V
- **Max Hp Rating:** 3 at 240 Vac Std. 1 Ph, 7.5 at 240 Vac Std. 3 Ph, 10 at 240 Vac TD 1 Ph, 15 at 240 Vac TD 3 Ph, 10 at 250 Vdc

Supporting documents:

- [DIMENSION DWG 30-200A NON-METALLIC SWITCHES](#)
- [Eatons Volume 2-Commercial Distribution](#)



- [Eaton Specification Sheet - DH322FCK](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.