



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Limit Switch Sensor

E55BLT1D

UPC:782114558577

Dimensions:

- **Height:** 1.57 IN
- **Length:** 4.64 IN
- **Width:** 1.57 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Limit Switch Sensor
- **Connection:** Screw Terminals
- **Contact Rating:** 400 mA at 250V
- **Contact Configuration:** 2-wire AC, NO or NC
- **Enclosure Material:** PBT resin
- **Environmental Rating:** NEMA 4, 4X, 6, 12, 13, IP67
- **Input Voltage:** 35-250V
- **Led Indicators:** Power ON, output ON
- **Maximum Ac Current:** 400 mA
- **Number Of Wires:** 2-wire
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** E55

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E55BLT1D](#)

Certifications: No Data

Product compliance: No Data



