



Powering Business Worldwide

pe.eaton.com

CLPT type current limiting fuse

5NCLPT-3E

UPC:782114610114

Dimensions:

- **Height:** 1.25 IN
- **Length:** 5.63 IN
- **Width:** 6.25 IN

Weight: .29 LB

Notes: Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** NCLPT
- **Barrels:** Single barrel (non-indicating)
- **Diameter:** .81 IN
- **Interrupt Rating:** 63 kA
- **Amperage Rating:** 3E
- **Class:** E
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 5NCLPT-3E](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

