



Powering Business Worldwide

pe.eaton.com

Nanoview Photoelectric Sensor

E71-SDP-M8

UPC:786685262222

Dimensions:

- **Height:** 1.41 IN
- **Length:** .79 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Connection:** M8
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Contact Configuration:** Complementary PNP open collector
- **Enclosure Material:** ABS UL 94V-0
- **Environmental Rating:** IP66
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output (yellow), stability (green), power (green)
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** S/C and reverse polarity
- **Sensor Type:** Diffuse Reflective
- **Series:** E71

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Introducing NanoView Series sensors](#)
- [Eaton Specification Sheet - E71-SDP-M8](#)

Certifications: No Data

Product compliance: No Data



