



Powering Business Worldwide

pe.eaton.com

E49 Series Mini Metal Limit Switch

E49G31CP3

UPC:786685102078

Dimensions:

- **Height:** 4.25 IN
- **Length:** 1.1 IN
- **Width:** .98 IN

Weight:.2438 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 250Vac, 5A at 30Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Head &Body: Zinc Alloy, Terminal Cover: ABS Plastic
- **Environmental Rating:** IP65
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 23° to 149°F (-5° to 65°C)
- **Switch Type:** Top Push Roller

Supporting documents:

- [E49 Mini Metal Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49G31CP3](#)

Certifications: No Data

Product compliance: No Data

