



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E49 Series Mini Metal Limit Switch

**E49G31XM3**

**UPC:**786685102146

### Dimensions:

- **Height:** 7.22 IN
- **Length:** 1.1 IN
- **Width:** .98 IN

**Weight:**.2563 LB

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 5A at 250Vac, 5A at 30Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Head &Body: Zinc Alloy, Terminal Cover: ABS Plastic
- **Environmental Rating:** IP65
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 23° to 149°F (-5° to 65°C)
- **Switch Type:** Wobble Stick, Cat Whisker

### Supporting documents:

- [E49 Mini Metal Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E49G31XM3](#)

**Certifications:** No Data

**Product compliance:** No Data

