



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E47 Precision Limit Switch, Basic

E47BMS40

UPC:782113771069

### Dimensions:

- **Height:** 1.94 IN
- **Length:** .75 IN
- **Width:** 2.11 IN

**Weight:**.1438 LB

**Notes:**Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 -12 AWG (2.5 sq. mm maximum)

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 125Vac / 15A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Mineral Filled Phenolic
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Switch Type:** Adj. Roller

### Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BMS40](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked



