



Powering Business Worldwide

pe.eaton.com

E65 Miniature Series Rectangular Body Photoelectric Sensor

E65CBL2

UPC:782114014226

Dimensions:

- **Height:** 2.04 IN
- **Length:** .51 IN
- **Width:** 1.1 IN

Weight:.28 LB

Notes:Ranges based on a 90% reflectance card

Warranties:

- 3 year

Specifications:

- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 100 mA at 30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** Wired for Either NPN or PNP Transistor Output
- **Cord Length:** 79.2 FT
- **Enclosure Material:** ABS Plastic
- **Environmental Rating:** NEMA 1,3,4,12,13, IP66
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Yes
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** 5° to 131°F (-15° to 55°C)
- **Protection:** Short circuit and transient
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E65CBL2](#)



Certifications:

- UL Recognized

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.