



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CN35 or A202 Enclosed Lighting Contactor

**ECL03D1E2A**

**UPC:**782114040287

### Dimensions:

- **Height:** 5.98 IN
- **Length:** 10.01 IN
- **Width:** 6 IN

**Weight:**7 LB

**Notes:** Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 60A
- **Coil Voltage:** 208V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 65 mm
- **Number Of Poles:** Two-pole
- **Type:** Non-combination electrically held

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03D1E2A](#)

### Certifications:

- cUL Listed
- UL Listed

**Product compliance:** No Data

