



Powering Business Worldwide

pe.eaton.com

Type CH 3/4-inch High-Ambient Circuit Breaker

CH250M50

UPC:782114021699

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Two-Pole 120/240V Common Trip Requires Two 3/4-Inch Spaces

Warranties: No Data

Specifications:

- **Type:** Type CH 3/4-inch High-Ambient Circuit Breaker
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CH
- **Trip Type:** Common
- **Wire Size:** (1) #14-8, (2) #14-10 AWG Cu/Al 60°C or 75°C
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CH250M50](#)

Certifications:

- UL 489

Product compliance: No Data

