



Powering Business Worldwide

pe.eaton.com

Series C, J-frame Molded Case Circuit Breaker

JD3250A06S10

UPC:786679033197

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 250A
- **Interrupt Rating:** 65 kAIC at 240V
- **Number Of Poles:** Three-pole
- **Auxiliary Switch:** 1A-1B right pigtail
- **Frame Size:** J-frame
- **Series:** Series C
- **Shunt Trip:** 110-240 Vac or 110-125 Vdc left pigtail rear
- **Trip Type:** Non-interchangeable thermal magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - JD3250A06S10](#)

Certifications:

- UL Listed

Product compliance: No Data



