



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH222NDK

UPC:782113205861

Dimensions:

- **Height:** 8.5 IN
- **Length:** 20 IN
- **Width:** 9.5 IN

Weight:22 LB

Notes:Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened. 3-phase hp ratings shown are grounded B phase ratings; UL listed.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 3 at 240 Vac Std. 1 Ph, 7.5 at 240 Vac Std. 3 Ph, 10 at 240 Vac TD 1 Ph, 15 at 240 Vac TD 3 Ph, 10 at 250 Vdc

Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)



- [Eaton Specification Sheet - DH222NDK](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.