



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Full Voltage Non-Reversing Starter

**BN16KN0A**

**UPC:**782114023280

### Dimensions:

- **Height:** 11.35 IN
- **Length:** 5.94 IN
- **Width:** 4.08 IN

**Notes:** Heater Packs must be purchased separately. For separate 120V control circuit. For maximum hp at listed motor voltages, use the rating of other starters of same size.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 120V
- **Horsepower:** 115 hp
- **Number Of Poles:** Two-pole
- **Phase:** Single-phase magnetic
- **Size:** 3
- **Series:** Freedom
- **Type:** Starter
- **Voltage Rating:** 120V at 60 Hz

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - BN16KN0A](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data



