



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Assembled Control Station

10250T3518

UPC:782113227146

Dimensions:

- **Height:** .055 IN
- **Length:** .036 IN
- **Width:** .05 IN

Weight:2 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Pushbutton, flush
- **Actuator Color:** Red
- **Contact Configuration:** 1NC
- **Enclosure Material:** Die cast
- **Legend:** STOP
- **Mounting:** Surface
- **Number Of Elements:** 1
- **Operating Mode:** Momentary
- **Rating:** NEMA 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T3518](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



