



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E50 Heavy Duty Factory Sealed 6P+ Limit Switch

**E50AM16P**

**UPC:**782113134727

### Dimensions:

- **Height:** 4.67 IN
- **Length:** 1.54 IN
- **Width:** 2.25 IN

**Weight:**2.1 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** Refer to installation publication P15836
- **Connection:** 8 Ft. ( 2.5m ) Cable
- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Cable Type:** SOOW-A
- **Contact Configuration:** 1NO-1NC
- **Cord Length:** 96 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 201°F (-10° to 94°C)
- **Switch Type:** Side Rotary, Maintained

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50AM16P](#)

### Certifications:

- UL Listed
- CSA Certified



**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.