



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH361FRKA1480

UPC:782116418237

Dimensions:

- **Height:** 16.27 IN
- **Length:** 9.89 IN
- **Width:** 7.75 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** 15A GFI receptacle
- **Type:** Single-Throw
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 7.5 at 480 Vac TD 1 Ph, 10 at 600 Vac TD 1 Ph, 15 at 480 Vac TD 3 Ph, 20 at 600 Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH361FRKA1480](#)

Certifications:



- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.