



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## FERRUPS UPS

FA000BB2A0A0A0A

UPC:790341042011

### Dimensions:

- **Height:** 12 IN
- **Length:** 21.25 IN
- **Width:** 10 IN

**Weight:**54 LB

### Warranties:

- 2 year

### Specifications:

- **Type:** Ferro-resonant UPS
- **Battery Type:** Standard battery, standard charger
- **Efficiency:** 85% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** (1) 5-15P
- **Operating Temperature:** 0° to 40°C
- **Output:** (2) 5-15R
- **Output Voltage:** 120V
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 500000 KVA
- **Cable Type:** Communication cable
- **Color:** Beige with blue highlights
- **Configuration:** Tower
- **Cord Length:** 864
- **Runtime:** 9 min full load, 25 min half load
- **Serial Interface:** RS-232 serial port, DB25, plus contact closures
- **Software:** LanSafe, PowerVision, Foreseer
- **Wattage:** 350W

**Supporting documents:**



- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FA000BB2A0A0A0A](#)

**Certifications:**

- CSA Certified
- ANSI/IEEE Std C62.41
- ANSI/IEEE Std C62.45
- IEC 801-4
- FCC Cat. A
- UL Listed
- IEC 801-5
- IEC 801-2

**Product compliance:** No Data