



Powering Business Worldwide

pe.eaton.com

Intelliview Photoelectric Sensor

E75-PPA025P-M12

UPC:786685262383

Dimensions:

- Height: X
- Length: X
- Width: X

Warranties:

- 3 year

Specifications:

- **Type:** Back Ground Suppression
- **Connection:** M12
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Output:** Light/dark selectable
- **Contact Configuration:** Complementary PNP open collector
- **Enclosure Material:** ABS
- **Environmental Rating:** IP65
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output (red), stability (green)
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Series:** E75

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Introducing IntelliView](#)
- [Eaton Specification Sheet - E75-PPA025P-M12](#)

Certifications: No Data

Product compliance: No Data



