



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

E51PLP1

UPC:782113124803

Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

Weight:.975 LB

Warranties:

- 3 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 600 mA
- **Contact Configuration:** Complementary PNP
Open Collector
- **Enclosure Material:** Receptacle and Body: Die
Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA
3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 10–30 Vdc
- **Led Indicators:** Lights when output is ON. One
red LED for each output
- **Operating Mode:** Non Polarized Retroreflective
- **Operating Temperature:** -13° to 158°F (-25° to
70°C)
- **Sensor Type:** Retroreflective
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51PLP1](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.