



Powering Business Worldwide

pe.eaton.com

Flat Tubular Contrast Photoelectric Sensor

E76-CNT010P-M12

UPC:786685262352

Dimensions:

- **Height:** .71 IN
- **Length:** 3.21 IN
- **Width:** .71 IN

Warranties:

- 3 year

Specifications:

- **Connection:** M12
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Contact Configuration:** Complementary PNP open collector
- **Enclosure Material:** PBT
- **Environmental Rating:** IP67
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output, ready/error
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Contrast detector
- **Operating Temperature:** 14° to 131°C
- **Sensor Type:** Contrast
- **Series:** E76

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Introducing IntelliView](#)
- [Eaton Specification Sheet - E76-CNT010P-M12](#)

Certifications: No Data

Product compliance: No Data



