



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Thermal-Magnetic Circuit Breaker

QHCX2100

UPC:786679151723

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.8 IN
- **Width:** 2.2 IN

Weight:.8 LB

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 100A
- **Interrupt Rating:** 42 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** QHCX
- **Connection:** Cable-in/Cable-out

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - QHCX2100](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

