



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH322NRKA1240

UPC:782116418367

Dimensions:

- **Height:** 15.88 IN
- **Length:** 10 IN
- **Width:** 8.13 IN

Weight:20 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** 15A GFI receptacle
- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 3 at 240 Vac Std. 1 Ph, 7.5 at 240 Vac Std. 3 Ph, 15 at 240 Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH322NRKA1240](#)

Certifications:

- UL Listed

Product compliance: No Data



