



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH362NRKA1480

UPC:782116418404

### Dimensions:

- **Height:** 15.88 IN
- **Length:** 10 IN
- **Width:** 8.13 IN

**Weight:**20 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** 15A GFI receptacle
- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 30 at 480 Vac TD 3 Ph, 50 at 600 Vac TD 3 Ph

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips](#)
- [Eaton Specification Sheet - DH362NRKA1480](#)



**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.