



Powering Business Worldwide

pe.eaton.com

Type C361 Flange Mounted Disconnect Switch

C361SD162

UPC:782113599243

Dimensions:

- **Height:** 9.5 IN
- **Length:** 18.7 IN
- **Width:** 11.5 IN

Notes:Maximum horsepower ratings refer to switch only. Fuse clips are non-interchangeable type for Class H, J, K, or R type fuses only. Components individually boxed and shipped in overpack carton.

Warranties:

- 1 year

Specifications:

- **Type:** Switch and operating mechanism with handle
- **Amperage Rating:** 60A
- **Depth Range:** 7-16 in
- **Enclosure:** NEMA 1 or 12
- **Fuse Clip Rating:** 60A at 600V
- **Handle Length:** 4 IN
- **Max Hp Rating:** 15 hp at 208 Vac, 15 hp at 240 Vac, 30 hp at 480 Vac, 50 hp at 600 Vac, 10 hp at 250 Vdc
- **Mounting:** Right-hand
- **Wire Size:** #2-14 AWG Cu/Al

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - C361SD162](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



