



Powering Business Worldwide

pe.eaton.com

C30CN Enclosed Lighting Contactor

ECC03C2A8A

UPC:782116162819

Dimensions:

- **Height:** 15.875 IN
- **Length:** 8.625 IN
- **Width:** 8.375 IN

Weight:20 LB

Notes: Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Eight-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECC03C2A8A](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

