



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Freedom Line Enclosed Control

**ECN1808CHC**

**UPC:**782114055854

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Enclosure:** NEMA 12
- **Type:** Combination non-reversing starter
- **Accessories:** With control power transformer
- **Actuator:** HAND/OFF/AUTO selector switch
- **Fuse Clip Rating:** 30A/600V
- **Fuse Clip Type:** Type R
- **Phase:** Three-phase
- **Size:** NEMA size 0
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN1808CHC](#)

### Certifications:

- UL Listed file E1491

**Product compliance:** No Data

