



Powering Business Worldwide

pe.eaton.com

Non Plug-in Style Assembled Limit Switch

10316H577

UPC:782113229676

Dimensions:

- **Height:** 5.18 IN
- **Length:** 1.55 IN
- **Width:** 1.78 IN

Weight:1.125 LB

Notes:Complete Assembled Switches; Consult factory for CE approval status

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 10A at 600Vac, 0.22A at 125Vdc
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 4, 13
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 0.22A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Top Push Roller

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H577](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



- Contact Manufacturer

© 2016 Eaton. All rights reserved.