



Powering Business Worldwide

pe.eaton.com

Current Limiting Fuse

15CLE-80E

UPC:786670001799

Dimensions:

- **Height:** .001 IN
- **Length:** .001 IN
- **Width:** .001 IN

Weight:.001 LB

Notes:Consult factory for mountings.

Warranties:

- Not Applicable

Specifications:

- **Type:** E-rated
- **Special Features:** Indoor/outdoor, single barrel
- **Application:** Indoor / Outdoor
- **Barrels:** Single barrel
- **Clip Center:** 20
- **Diameter:** 3 IN
- **Interrupt Rating:** 63 kA
- **Series:** CLE
- **Amperage Rating:** 65A
- **Class:** E
- **Maximum Voltage:** 15.5 kV
- **Nominal Voltage:** 14.4 kV

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 15CLE-80E](#)

Certifications:

- IEEE Std. C37.41
- Not Applicable

Product compliance:

- Contact Manufacturer



