



Powering Business Worldwide

pe.eaton.com

Comet Series Tubular Photoelectric Sensor

13100RQD07

UPC:782113843568

Dimensions:

- **Height:** 2.55 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.1313 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA PNP, 250 mA NPN at 10-30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN and PNP Open Collector
- **Cord Length:** 8 IN
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA PNP, 250 mA NPN
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset short circuit
- **Switch Type:** Photoelectric



Supporting documents:

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13100RQD07](#)

Certifications:

- cUL Recognized
- UL Recognized

Product compliance:

- CE Marked
- Contact Manufacturer