



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Transformer

**V29M22T30EE**

**UPC:**786680046971

**Dimensions:**

- **Height:** 30 IN
- **Length:** 16.5 IN
- **Width:** 23 IN

**Weight:**318 LB

**Notes:**NEMA TP-1 efficient

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Dry Type Distribution Transformer
- **Design:** DT-3
- **Coil Material:** Aluminum windings
- **Frame:** 912B
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 208V
- **Secondary Voltage:** 240 delta/120 midtap
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 30 KVA
- **Weathershield:** WS38

**Supporting documents:**

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - V29M22T30EE](#)

**Certifications:**

- UL Listed

**Product compliance:**



- NEMA TP-1 Compliant

---

© 2016 Eaton. All rights reserved.