



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Harsh Environment Non-Metallic Safety Switch

**DH363FCK**

**UPC:**782114296059

### Dimensions:

- **Height:** 27.25 IN
- **Length:** 16.46 IN
- **Width:** 14.25 IN

**Notes:** Suitable for service entrance use with a neutral or ground lug kit installed

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 100A
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Non-metallic
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Harsh Environment - EnviroLine
- **Voltage Rating:** 600V
- **Max Hp Rating:** 30 at 480 Vac TD 1 Ph, 40 at 600 Vac TD 1 Ph, 60 at 480 Vac TD 3 Ph, 75 at 600 Vac TD 3 Ph

### Supporting documents:

- [DIMENSION DWG 30-200A NON-METALLIC SWITCHES](#)
- [Eatons Volume 2-Commercial Distribution](#)



- [Eaton Specification Sheet - DH363FCK](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.