



Powering Business Worldwide

pe.eaton.com

Type BR Style 1-inch Plug-On Circuit Breaker

BRH325

UPC:786676002707

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 3 IN

Weight:2 LB

Notes:10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Amperage Rating:** 25A
- **Interrupt Rating:** 22 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Mounting:** Plug-on
- **Main Circuit Breaker:** BRH
- **Trip Type:** Common
- **Wire Size:** #14-4 AWG Cu/Al at 60°C or 75°C
- **Quantity:** 5
- **Used With:** Type BR Loadcenters

Supporting documents:

- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BRH325](#)

Certifications:

- UL 490

Product compliance:

- Federal Specifications Classification W-C376



