



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH227NWK

UPC:782113589770

Dimensions:

- **Height:** 71.75 IN
- **Length:** 12.75 IN
- **Width:** 24.9 IN

Notes:3-Phase hp ratings shown are grounded B phase ratings; UL listed

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 800A
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Stainless steel
- **Fuse Class Provision:** Class L fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 100 at 240 Vac Std. 3 Ph, 250 at Vac TD 3 Ph

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH227NWK](#)

Certifications:

- UL Listed

Product compliance: No Data



