



Powering Business Worldwide

pe.eaton.com

Continuous Duty AC Solenoid

10370H70

UPC:782113236100

Dimensions:

- **Height:** 4.88 IN
- **Length:** 3 IN
- **Width:** 3.13 IN

Notes: Mounting of solenoids “with conduit box”—Size A are for wall mounting—Size B, C and D are for floor mounting.

Warranties:

- 1 year

Specifications:

- **Magnetic Force Against Gravity:** 3.9 lbs at 100% voltage, 2.7 lbs at 85% voltage
- **Magnetic Force Horizontal:** 4.2 lbs at 100% voltage, 3 lbs at 85% voltage
- **Magnetic Force With Gravity:** 4.5 lbs at 100% voltage, 3.3 lbs at 85% voltage
- **Frequency Rating:** 60 Hz
- **Full Load Current Range:** Inrush 5.4A/Sealed .87A
- **Mounting:** Floor mount
- **Operation:** Pull type
- **Size:** B
- **Special Features:** With conduit box
- **Voltage Rating:** 220A

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 10370H70](#)

Certifications: No Data

Product compliance: No Data



