



Powering Business Worldwide

pe.eaton.com

Comet Series Tubular Photoelectric Sensor

13103RQD03

UPC:782116128761

Dimensions:

- **Height:** 3.02 IN
- **Length:** .57 IN
- **Width:** .71 IN

Weight:.1313 LB

Warranties:

- 3 year

Specifications:

- **Connection:** 4 Pin Dual Key Micro Connector
- **Contact Rating:** 300 mA AC/DC at 20-264Vac/15-30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** AC: L1 Switched, DC: NPN Open Collector
- **Cord Length:** 8 IN
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: Polycarbonate
Cable Jacket: PVC Body: Structural Polyurethane Foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13, IP68, IP69K
- **Input Voltage:** 20-264 Vac/15-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 300 mA
- **Operating Mode:** Background Suppression
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Latching short circuit
- **Sensor Type:** Back Ground Suppression
- **Switch Type:** Photoelectric



Supporting documents:

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13103RQD03](#)

Certifications: No Data**Product compliance:**

- Contact Manufacturer

© 2016 Eaton. All rights reserved.