



Powering Business Worldwide

pe.eaton.com

FERRUPS UPS

FG010AA0A0A0A0B

UPC:743172067043

Dimensions:

- **Height:** 21.2 IN
- **Length:** 22.9 IN
- **Width:** 15.25 IN

Weight:188 LB

Warranties:

- 2 year

Specifications:

- **Efficiency:** 90% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** Hardwired
- **Operating Temperature:** 0° to 40°C
- **Phase:** Single-phase
- **Topology:** Ferroresonant
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 2100 KVA
- **Cable Type:** Communication cable
- **Color:** Beige with blue highlights
- **Communication:** RS-232 serial port, DB-25
- **Configuration:** Tower
- **Runtime:** 9 min full load, 25 min half load
- **Software:** Powerware software suite
- **Wattage:** 1.5 kW

Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FG010AA0A0A0A0B](#)

Certifications:

- IEC 801-5



- UL Listed
- FCC Cat. A
- ANSI/IEEE Std C62.41
- ANSI/IEEE Std C62.45
- IEC 801-4
- CSA Certified
- IEC 801-2

Product compliance: No Data

© 2016 Eaton. All rights reserved.