



Powering Business Worldwide

pe.eaton.com

Adjustable Frequency Drive

SPX100A1-2A1B1

UPC:782116897117

Dimensions:

- **Height:** 45.3 IN
- **Length:** 13.4 IN
- **Width:** 18.9 IN

Weight:322 LB

Warranties:

- 2 year

Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR9
- **Horsepower:** 100 hp
- **Rating:** NEMA Type 1/IP21
- **Software:** Standard Software
- **Voltage Rating:** 230V

Supporting documents:

- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX100A1-2A1B1](#)
- [Product Datasheet - SPX100A1-2A1B1](#)

Certifications:

- IEC 61800-2
- EN 61800-3 Level H
- UL 508C
- UL Listed

Product compliance: No Data



