



Powering Business Worldwide

pe.eaton.com

E47BCC Series Compact Pre-Wired Limit Switch

E47BCC07P4

UPC:786685293264

Dimensions:

- **Height:** 2.64 IN
- **Length:** 1.58 IN
- **Width:** .69 IN

Weight:.32 LB

Warranties:

- 1 year

Specifications:

- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 5A at 240 Vac/5A at 14 Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 4, 6 and 13 IEC IP67
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 14° to 158°F (-10° to 70°C)
- **Switch Type:** Roller Plunger

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BCC07P4](#)

Certifications: No Data

Product compliance: No Data

