



Powering Business Worldwide

pe.eaton.com

Group Metering Main Circuit Breaker

1MHCBE1200R

UPC:782116136735

Dimensions:

- **Height:** 20 IN
- **Length:** 60 IN
- **Width:** 25 IN

Weight:210 LB

Notes:If additional neutral lugs are needed, order 1MCB1200NLK [(3) 1/0-750 kcmil or (6) 1/0-300 kcmil].

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** EUSERC
- **Amperage Rating:** 1200A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Underground
- **Interrupt Rating:** 100 kAIC
- **Main Circuit Breaker:** NGH
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V
- **Wire Size:** Crimp lug landing pads (no lugs included)

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - 1MHCBE1200R](#)



Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.