



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Adjustable Frequency Drive

**SPX350A0-4A2B1**

**UPC:**782116342877

### Dimensions:

- **Height:** 45.9 IN
- **Length:** 19.9 IN
- **Width:** 19.7 IN

**Weight:**518 LB

### Warranties:

- 2 year

### Specifications:

- **Brake Chopper:** Brake chopper
- **Input:** Three-phase, EMC N
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR10
- **Horsepower:** 350 hp
- **Software:** Standard Software
- **Voltage Rating:** 480V

### Supporting documents:

- [Eaton's Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX350A0-4A2B1](#)
- [Product Datasheet - SPX350A0-4A2B1](#)

### Certifications:

- IEC 61800-2
- UL 508C
- UL Listed
- EN 61800-3 Level H

**Product compliance:** No Data



