



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL04F1A4A

UPC:782114063767

Dimensions:

- **Height:** 28.313 IN
- **Length:** 13.188 IN
- **Width:** 11.563 IN

Weight:41 LB

Notes:When using three-position selector switch, mod C20 must also be used (ECL04, ECL13, ECL15). Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 200A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Frame Size:** 180 mm
- **Number Of Poles:** Four-pole
- **Type:** Non-combination mechanically held and magnetically latched

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL04F1A4A](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data



