



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH262FDK

UPC:782113206097

### Dimensions:

- **Height:** 8.5 IN
- **Length:** 20 IN
- **Width:** 9.5 IN

**Weight:**22 LB

**Notes:**Suitable for service entrance use with a neutral or ground lug kit installed. Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Two-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 600V
- **Max Hp Rating:** 20 at 480 Vac TD 1 Ph, 25 at 600 Vac TD 1 Ph, 25 at 600 Vdc

### Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH262FDK](#)



**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.