



Powering Business Worldwide

pe.eaton.com

200 Series Zero Pressure Accumulation Photoelectric Sensor

14266RLN17B1

UPC:782114415900

Dimensions:

- **Height:** 1.45 IN
- **Length:** 1.19 IN
- **Width:** 1.73 IN

Weight:.0563 LB

Notes:Output protected against dead shorts only; will not protect against overloads between 100-300mA

Warranties:

- 3 year

Specifications:

- **Connection:** 5 Pin AMP Connector
- **Contact Rating:** 100 mA at 30Vdc
- **Contact Configuration:** NPN Open Collector
- **Enclosure Material:** Cyclopol and Lexan
- **Environmental Rating:** NEMA 1
- **Led Indicators:** Red zone status, on when valve output is on
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Polarized Retroreflective
- **Operating Temperature:** 14° to 131°F (-10° to 55°C)
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 14266RLN17B1](#)

Certifications: No Data

Product compliance:



- Contact Manufacturer

© 2016 Eaton. All rights reserved.